# Specifications of INDITHERM ® burners

#### Typical burner data

Fuel: natural gas at 60° F with 1000 Btu/ft<sup>3</sup> (st) HHV - sg = 0.6 [1] Combustion air:  $60^{\circ}$  F - 21 %  $O_2$  - 50 % humidity - sg = 1.0 [1]


Stated pressures are indicative. Actual pressures are a function of air humidity, altitude, type of fuel, and gas quality.

·		•				•				•	~
Burner size & type			100	200	300	550	700	850	1100	1500	1800
		back pres- sure [2] "w.c.									
May consoity to	MBtu/h	0	0.43	0.79	1.15	1.88	2.56	2.90	3.58	5.02	6.14
Max. capacity [3]	IVIDIU/II	0.6	0.38	0.70	0.94	1.71	2.30	2.64	3.00	4.32	5.39
Min. capacity [4]	KBtu/h	0-0.6	22	19	15	34	58	51	154	85	85
Pilot capacity [5]	KBtu/h	0-0.6	26	24	34	51	85	85	154	136	136
Combustion air differential	"w.c.	0	2.6	2.3	1.8	2.4	3.1	3.6	2.0	2.6	5.2
pressure [6]		0.6	2.0	1.8	1.3	2.0	2.9	3.0	1.4	1.9	4.6
Combustion air flow		0	80	137	212	353	436	536	647	948	1089
Combustion all now	scfm	0.6	70	119	173	321	428	489	541	816	971
Gas differential pressure at inlet [7]	"W.C.	0	1.2	1.8	3.0	2.3	3.4	4.8	7.1	2.1	3.8
Gas differential pressure at	"w.c.	0	1.0	1.3	2.4	1.9	2.4	4.3	6.3	2.0	3.5
test connection [8]	vv.C.	0.6	0.8	1.0	1.7	2.2	2.3	3.7	4.5	1.5	3.0
Flame length [9]	ft	0-0.6	3	4.5	3.5	6	6.3	6	7	7.8	9-12

- [1] sg (specific gravity) = relative density to air (density air = 0.0763 lb/ft<sup>3</sup>(st).
- [2] Back pressure = static pressure in the combustion chamber where the flame develops. Data in this table are given for0and 0.6 "w.c.back pressure.Combustion air flow valid for all listed maximum capacities.
- [3] Maximum capacity when firing at 3% vol. O<sub>2</sub> level in the flue gas.
- [4] Minimum capacity without pilot gas. If lower minimum capacities are required, refer to chapter 'minimum capacities' in this section.
- [5] With direct ignition (no pilot), start capacity should be equal or higher than the stated pilot capacity.
- [6] Differential pressure measured between burner test connection and combustion chamber.
- [7] Gas differential pressures for natural gas at burner inlet. This pressure should be available at burner inlet throughout the entire capacity range.
- [8] Differential pressure to be measured between burner test connection and combustion chamber.
- [9] Flame lengths are derived from measured lab data. Actual flame lengths can differ slightly.



# **Materials of construction**



1	Housing	Cast iron
2	Standard sleeve	AISI 310 (1.4841)
_	High temperature block	Castable refractory
3	Blower housing	Carbon steel
4	Motor mounting bracket	Carbon steel



### **Selection criteria**

#### **Application details**

Because of the burner's versatility there are numerous types of applications for INDITHERM <sup>®</sup> burners. All types of indirect-fired applications can be equipped with this simple, industrial burner. Among the major applications there are automotive paint-bake ovens and surface treatment, bakery ovens and dryers for the food industry.

Available INDITHERM ® burner versions and options

INDITHERM® burners are designed to operate on natural gas only.

All burners are available in ANSI and ISO version. Each version will have the main gas inlet connection following either NPT or ISO standards

All burners include an adjustable orifice needle valve for pilot flame fine tuning, provision for UV scanner connection and a stainless steel combustion sleeve.

#### **Options**

Every burner has a set of options available, according to the table below:

HTS	High temperature discharge sleeve
FLR	Combustion air filter box, recommended in extremely dusty surroundings
DI	Direct ignited: in this case the adjustable orifice will be removed and the pilot connection at the burner will be plugged
UVC	Burner flame scanner connection prepared for UV scanner mounting (scanner not included)
CBL	Connecting bracket and linkage for control motor mounting (control motor make and type to be specified)

#### Exception:

FR	Flame rod, only to be used in limited number of applications, see
ГК	page 1-2.3-11



The spark ignitor is standard included on the burner.



### **Burner designation**

Burner type	Burner size	Burner gas connection	Discharge sleeve	Ignition	Flame supervision
INDITHERM ®	300	ISO	HTS	DI	UVC

Burner size 100 200 300	Discharge sleeve HTS: High temperature STD: standard version, stainless steel
550 700 850 1100	Ignition DI: Direct Ignition (plugged pilot port) PL: Pilot burner
1500 1800	Flame supervision UVC: prepared for UV scanner mounting FRC: prepared for flame rod mounting

## Burner gas connection

ISO: ISO threated NPT: NPT threaded


#### **Fuels**

INDITHERM <sup>®</sup> burners are designed to operate on natural gas. For propane and butane operation a standard INDITHERM <sup>®</sup> burner can not be used. Contact MAXON when the use of gases other than natural gas is inevitable.

### Burner discharge sleeve

The burner discharge sleeve is available in different materials and geometries:

- Standard version with circular stainless steel discharge sleeve and square burner mounting plate.
- High temperature version with refractory block for installation in applications where high temperatures can be expected.



In following cases the use of high temperature version discharge sleeve is required:

- Dimension A is larger than 2"
- Insufficient low temperature process air is available to cool the discharge sleeve
- No process air is available (typical in indirect fired applications)
- Process air is entered downstream of the burner, being unable to flow over the burner discharge sleeve



#### Control motor mounting plate

The INDITHERM <sup>®</sup> burner can be equipped with an electrical or pneumatic control motor for capacity control. A broad range of mounting plates are available to accept almost any common control motor on the market. Required torque = 1.2 Nm.

### **Maximum capacities**

INDITHERM <sup>®</sup> burners will have different maximum capacities depending on burner size and application back pressure. Refer to table on page 1-2.3-6 for maximum capacities.

Capacities are stated for firing at zero back pressure and for 0.6 "w.c. back pressure, both at 3 % O<sub>2</sub> level in the exhaust gases.

#### Minimum capacities

The minimum capacities depend on burner size and can be found in the table at page 1-2.3-6. The capacities in this table are those that still allow a stable flame on main gas. When lower capacities are required, using a continuous pilot can be a solution. In this case, the internal gas control valve of the burner can be closed even more at minimum position, while the minimum required gas flow to maintain a stable flame can be adjusted using a needle valve on the pilot gas.

#### Preheated air

The INDITHERM <sup>®</sup> burner is designed to operate with non preheated combustion air. Although, the burner materials are suitable to withstand up to 400 °F temperatures, the burner will not perform according to the specifications page page 1-2.3-6 when the combustion air is preheated. Contact MAXON for more details.

#### **Process temperature**

The high temperature refractory block permits operation of combustion chamber temperatures up to 1750 °F. When using a standard discharge sleeve, proper circulation of cold process air around the entire discharge sleeve should be present at all times.

### **Piloting and ignition**

INDITHERM <sup>®</sup> burners have an internal pilot burner. Piloting is accomplished by internally bypassing the built-in gas butterfly valve which is in the minimum position at low fire. The pilot gas is admitted to the gas nozzle via the main gas conduit and is injected through the same gas nozzle ports as the main gas. The pilot gas adjusting valve allows for easy and precise adjusting of the pilot flame.

The use of an intermittent pilot is technically possible on this burner and could result in lower minimum capacities.

Use minimally 5000 V/200 VA ignition transformers for sparking of the spark ignitor. Locate pilot gas valves as close as possible to the pilot burner gas inlet, to have fast ignition of the pilot burner. When igniting the main gas, the capacity rating of the burner at that point shall be limited.

#### **Direct ignition**

In case the use of a pilot burner is not required, the INDITHERM <sup>®</sup> burner can be direct ignited on main gas.

The pilot gas inlet should be plugged. When direct igniting an INDITHERM <sup>®</sup> burner, the capacity setting during ignition should be limited. Direct ignition at high capacity is not allowed.



#### Typical ignition sequences

- Pre purge of burner and installation, according to the applicable codes and the installation's requirements.
- Burner capacity control valve shall be in the start position to allow minimum combustion air flow to the burner.
- Pre-ignition (typically 2 s sparking in air).
- Open pilot gas and continue to spark the igniter (typically 5 s).
- Stop sparking, continue to power the pilot gas valves and start flame check.
- Check pilot flame stability (typical 5 s to prove the stable pilot).
- Open main gas valves and allow enough time to have main gas in the burner. (typical 5 s + time required to have main gas in the burner).
- Close the pilot gas valves.
- Release to modulation (allow modulation of the burner).
- Above sequences shall be completed to include all required safety checks during the start-up of the burner (process & burner safeties).

#### Flame supervision

Flame supervision can be accomplished by use of a UV scanner for all INDITHERM <sup>®</sup> burners and sizes. The scanner connection is 1". Due to the presence of gas at the scanner port, only tight scanners can be used.

The use of a flame rod is only possible in a limited range of applications where the standard discharge sleeve is used. A flame rod combined with a high temperature discharge sleeve would generate a flame signal too low for proper flame scanning. Contact MAXON for more details when considering a flame rod.

#### Flame development

INDITHERM <sup>®</sup> burners shall be installed in combustion chambers that allow full development of the burner flame. Consult MAXON for proper combustion chamber lay-out.

#### Gas pipe train design

The INDITHERM <sup>®</sup> burner is very sensitive to variations in gas pressures at burner gas inlet. The burner gas inlet pressure should not vary more then 1"w.c. between high and low capacity.

#### **Process back pressures**

The INDITHERM <sup>®</sup> burner can operate between 0 and 0.6 "w.c. back pressure. The burner should not be used on applications where back pressures would fall outside these limits. It is possible to mount the burner on a process with changing back pressures as long as the fluctuating pressures stay within the to 0.6 "w.c. limit.

#### Measuring equipment for burner commissioning


The burner gas pressures and air pressures as mentioned in table on page 1-2.3-6 should be used as a guideline for burner system design and to have an approximative value for burner set up. To adjust the burner properly during commissioning, the oxygen content in the flue gas should be measured. A properly adjusted burner in an indirect fired application should have approximately 3%  $O_2$  in the stack at maximum capacity.



# **Dimensions**

# INDITHERM <sup>®</sup> with standard discharge sleeve - all sizes

- 1) Gas inlet
- 2) Pilot gas connection
- 3) Combustion air test connection
- 4) Gas pressure test connection
- 5) 90° capacity control crank
- 6) Filter housing (optional)
- 7) Stainless steel discharge sleeve (standard)
- 8) Flame supervision port
- 9) Spark ignitor




	Dimensions in inches unless stated otherwise																	
burner size	gas inlet [1]	А	В	С	ØD	Е	F	G	Н	I	J	К	L	М	N	ØР	s	Weight (kg)
100	1"	14.4	8.9	7.9	6.3	4.4	17.4	3.7	15.4	17.0	8.8	11.4	13.9	7.2	8.4	0.5	0.2	66
200	1"	14.4	8.9	7.9	6.3	4.4	17.4	3.7	15.4	17.0	8.8	11.4	13.9	7.2	8.4	0.5	0.2	66
300	1 - 1/4"	14.4	8.9	7.9	8.3	4.4	17.4	3.6	15.4	17.0	8.8	11.4	13.9	8.9	10.4	0.5	0.2	75
550	1 - 1/2"	20.2	10.0	7.9	10.2	5.4	21.3	3.9	17.1	18.2	12.1	14.4	15.7	11.3	12.5	0.5	0.3	110
700	2"	23.5	10.0	7.9	10.2	5.4	30.9	2.8	17.1	19.7	15.2	15.9	17.6	11.3	12.5	0.5	0.3	110
850	2"	23.5	10.0	7.9	10.2	5.4	30.6	2.8	18.3	19.6	15.2	15.9	17.6	11.3	12.5	0.5	0.3	110
1100	2"	23.5	14.4	7.9	12.2	6.5	30.6	5.4	22.0	23.3	15.2	15.9	17.6	13.4	14.8	0.5	0.3	154
1500	2"	23.5	14.4	7.9	12.2	6.5	30.6	5.4	22.0	23.3	15.2	15.9	17.6	13.4	14.8	0.5	0.3	154
1800	3"	25.9	14.4	7.9	12.2	6.5	31.9	5.4	23.8	26.1	17.8	17.8	18.9	13.4	14.8	0.5	0.3	154


[1] gas inlet is threaded, available in ISO or NPT.



# INDITHERM <sup>®</sup> with high temperature discharge sleeve - all sizes

- 1) Gas inlet
- 2) Pilot gas connection
- Combustion air test connection
- 4) Gas pressure test connection
- 5) 90° capacity control crank
- 6) Filter housing (optional)
- 7) High temperature discharge sleeve
- 8) Flame supervision port
- 9) Spark ignitor





	Dimensions in inches unless stated otherwise																	
burner size	gas inlet [1]	А	В	С	ØD	Е	F	G	Н	ı	J	К	L	ØМ	ØN	ØР	s	Weight (kg)
100	1"	14.4	9.1	7.9	10.1	4.4	17.4	3.3	15.6	17.2	8.8	11.4	13.9	12.6	14.1	0.6	0.5	100
200	1"	14.4	9.1	7.9	10.1	4.4	17.4	3.3	15.6	17.2	8.8	11.4	13.9	12.6	14.1	0.6	0.5	100
300	1 - 1/4"	14.4	9.1	7.9	12.0	4.4	17.4	3.9	15.6	17.2	8.8	11.4	13.9	14.5	15.9	0.6	0.5	125
550	1 - 1/2"	20.2	10.2	7.9	14.1	5.4	21.3	4.1	17.3	18.3	12.1	14.4	15.7	16.5	18.0	0.6	0.5	180
700	2"	23.5	10.2	7.9	14.1	5.4	30.9	3.0	17.3	19.8	15.2	15.9	17.6	16.5	18.0	0.6	0.5	180
850	2"	23.5	10.2	7.9	10.2	5.4	30.6	3.0	18.5	19.8	15.2	15.9	17.6	16.5	18.0	0.6	0.5	180
1100	2"	23.5	14.5	7.9	16.1	6.5	30.6	5.5	22.2	23.5	15.2	15.9	17.6	18.5	20.0	0.6	0.5	240
1500	2"	23.5	14.5	7.9	16.1	6.5	30.6	5.5	22.2	23.5	15.2	15.9	17.6	18.5	20.0	0.6	0.5	240
1800	3"	25.9	14.5	7.9	16.1	6.5	31.9	5.5	24.0	26.3	17.8	17.8	18.9	18.5	20.0	0.6	0.5	240
200	1"	365	5 232	2 20	0 25	7 11	1 442	2 10	0 397	438	224	289	353	320	357	14	12	47

[1] Gas inlet is threaded, available in ISO or NPT.





# Adjustable orifice for pilot burner - ADJ-ORF

This orifice is standard included with the burner and is factory mounted onto the burner pilot gas port. In case a burner has been ordered for direct ignition, this adjustable orifice is omitted.



- 2) Gas inlet 3/8" NPT
- Protection cap: remove to access flowadjustmentscrew HEX 3.8 mm





А	В	С
1.50"	3.44"	0.75"

Two available versions depending on burner size:

- ADJ-ORF-STD: with standard drilling for burner sizes 100, 200 and 300
- ADJ-ORF-HC: with larger internal drilling for burner sizes 550 and up




# Spark ignitor - SI-1/2

The spark ignitor is standard included with the burner. It is advised to keep at least one additional spark ignitor available as a spare item for maintenance.

This spark ignitor can be mounted directly onto the burner spark ignitor connection port.

To be used on all burner sizes. See table below for mounting position C depending on burner size.



1) 1/2" NPT

Dimensions in inches unless stated otherwise											
burner size	А	В	С	D	ØE						
100	6.50	5.51	1.30	0.20	0.55						
200	6.50	5.51	1.30	0.20	0.56						
300	6.50	5.51	1.46	0.20	0.55						
550-850	6.50	5.51	1.22	0.20	0.55						
1100-1800	6.50	5.51	1.30	0.20	0.55						

### Filter Elements - FLT- INDI

Replacement elements for the optional INDITHERM  $^{\circledR}$  burners combustion air filters. Available in 4 types to cover all burner sizes.

- FLT-INDI-1 for burner sizes 100,200 and 300
- FLT-INDI-2 for burner size 550
- FLT-INDI-3 for burner sizes 700-850-1100-1500
- FLT-INDI-4 for burner size 1800



### Gaskets - GSK- INDI

These gaskets are used to seal the mounting plate of the burner and the duct wall. Optionally available in 2 different types:

- GSK-INDI-STD to be used in combination with standard discharge sleeves (square)
- GSK-INDI-HT to be used in combination with high temperature discharge sleeves (round)

Gasket type	Burner Type	Geometry
GSK-INDI-STD-1	100 - 200	square
GSK-INDI-STD-2	300	square
GSK-INDI-STD-3	550-850	square
GSK-INDI-STD-4	1100-1800	square
GSK-INDI-HT-1	100	round
GSK-INDI-HT-2	300	round
GSK-INDI-HT-3	550-850	round
GSK-INDI-HT-4	1100-1800	round



# Installation and operation instructions for INDITHERM ® burners

### **Application requirements**

Supporting burner air and gas piping

The INDITHERM <sup>®</sup> burner shall not be used as support for the piping to the burner. Gas and air piping shall be supported in such a way that no additional loads will be created on the burner.

**Burner mounting flange loads** 

Check burner weight and reinforce burner mounting flange or combustion chamber/furnace back wall if necessary to support the complete burner weight.

Installation instructions

Storage of INDITHERM ® burners

INDITHERM <sup>®</sup> burners shall be stored dry (inside). Burner blocks have been cured carefully before shipment and shall be kept dry. Wetting of the blocks could result in premature failures.

Handling of INDITHERM ® burners

INDITHERM <sup>®</sup> burners are shipped as complete units. Handle burners with care, using proper equipment during unpacking, transport, lifting and installation. Any impact on the burner could result in damage. To prevent damage in transit, accessories such as flame rods, control valves, UV scanners, may be packed separately and shipped loose.

Orientation of INDITHERM ® burners


INDITHERM <sup>®</sup> burners can be mounted and fired in any direction. However we advise to avoid orientations which can permit flame supervision ports to collect debris and/or moisture. Also check limitations on orientation of other components mounted on the burner head.

**Burner mounting** 


Bolt the burner to the installation's burner mounting flange. Use proper gaskets between burner and burner mounting flange (option available). Tighten the flange bolting with correct torque. Retighten all bolts after first firing and regularly after commissioning.




# INDITHERM ® with standard sleeve



- 1) oven wall
- 2) mounting studs
- 3) gasket
- 4) burner



# INDITHERM <sup>®</sup> with block with seal and support housing



- 1) oven wall
- 2) mounting studs
- 3) gasket
- 4) burner







### **Burner mounting flange**

Refer to below figure to design a correct burner mounting flange on the installation.

Mounting flange for INDITHERM  $^{\circledR}$  burners with standard sleeve







200	184	214	185	M10

Dimensions in inches unless stated otherwise						
Burner size	А	В	ØС	D		
100	7.2	8.4	7.3	M10		
200	7.2	8.4	7.3	M10		
300	8.9	10.4	9.3	M10		
550	11.3	12.5	11.2	M10		
700	11.3	12.5	11.2	M10		
850	11.3	12.5	11.2	M10		
1100	13.4	4.8	13.2	M10		
1500	13.4	4.8	13.2	M10		
1800	13.4	4.8	13.2	M10		









Dimensions in inches unless stated otherwise						
Burner size	Ø A	ØВ	ØС	D		
100	11	12.6	14	M12		
200	11	12.6	14	M12		
300	13	14.5	16	M12		
550	15	16.5	18	M12		
700	15	16.5	18	M12		
850	15	16.5	18	M12		
1100	17	18.5	20	M12		
1500	17	18.5	20	M12		
1800	17	18.5	20	M12		
200	282	320	357	M12		