
FOOD, DAIRY & PHARMACEUTICAL

Configuration Code FD05 Thermometer Replacement RTDs

Thermometer replacement RTD temperature sensor assemblies are used when converting instrumentation from older direct reading thermometers to electronic instruments requiring RTD inputs. These RTD assemblies replace the filled system capillary actuating bulbs and will fit into the old existing bulb wells as listed below. These 3-wire constructed sensor assemblies consist of a high-accuracy platinum element sealed inside a spring-loaded 316 stainless steel sheath and are supplied with a FDA-compliant white thermoplastic gasketed head. Each sensor is supplied with a free-rotating stainless steel mounting fitting with the appropriate threading for the wells listed below.



ORDER CODES

Example Order Number:

1 2 3 R5T185L483 - 09(1/2) - TR - 63, I

1 Pt100 (α = 0.003 85 °C-1) RTD Assemblies

CODE	TOLERANCE[1]	
SINGLE	DUPLEX	TOLLKANGL
R1T185L483	R1T285L483	Grade B
R3T185L483	R3T285L483	Class AA
R5T185L483	R5T285L483	(1/5) Class B
RAF185L483	RAF285L483	Class A

[1] Refer to RTD tolerance information in the General Information section for calculations to determine specific tolerance at temperature.

Thermocouple Assemblies

For thermocouple assemblies use T/C types J, K, T, or E and options G for grounded junction or U for ungrounded junction as per example. EX.: TP48G - 09 (1/2) - TR - 63.

2 Immersion Length "X"

Specify "X" length in inches using 2 digits, plus any fractional length desired. Examples: 04 = 4", 05(1/2) = 5.5

3 Terminations

CODE	DESCRIPTION	
91	316L stainless steel screw-cover head	
63	White polypropylene screw-cover head	
31,W	Aluminum screw-cover head with white epoxy coating	
35T- 642A	(4 to 20) mA HART® Field Transmitter with aluminum general-purpose housing	
36T82- D10	(4 to 20) mA dual input HART® transmitter with digital display and general-purpose aluminum housing with glass lid	
37T- 662A	(4 to 20) mA HART® Field Transmitter with general- purpose aluminum housing	
Head Options		
T-440	(4 to 20) mA head-mounted RTD transmitter	
T-441	(4 to 20) mA isolated head-mounted transmitter	
T-442	(4 to 20) mA isolated HART® head-mounted transmitter	
T82-00	(4 to 20) mA dual input HART® head-mounted transmitter	
I	Stainless steel tags	
HS	Head supplied w/wire seal security screw	

Immersion Length "X"

"X" IMMERSION LENGTH ^[1]	LENGTH AND MOUNTING FITTING TO FIT BELOW LISTED WELL PART NUMBER		MOUNTING FITTING THREAD
(inches)	TAYLOR	ANDERSON	
9 (1/2)	26P397	41247	1 (1/4)"-18 UNEF
12 (1/2)	26P398	41279	1 (1/4)"-18 UNEF
11 (1/2)	SK10274	41280	1 (1/4)"-18 UNEF

[1] "X" dimension indicates length with spring in its fully expanded position. Spring will retract 1/2" minimum to 3/4" maximum.

HART® is a registered trademark of HART Communication Foundation.

